

Table of Contents

ompany information	UZ
Sustomer Service	04
AATImil Fabrics	06
AATImil Weave Types	80
AATImil PA GG	10
AATImil PA XXX	12
AATImil PA HT	14
AATImil PA XX	16
AATImil PA HS	18
AATImil PES GG	20
AATImil MAR	22
AATImil STS	24
abricated Components	26
AATImil Connector Sleeves	28
AATI Tendimesh Stretching System	30
AATImil Tension Meter	34
AATImil Adhesvies	35
ilip Screen Cleaners	38
ieve Cleaners	40
AATImil Accessories	44
nteractive Product Index	46
Contact Information	BACI

Engage with SAATI















-SAATI

Perfecting the Art of Precision Woven Mesh



Company Information

Over Eighty Years of Innovative Action

SAATI is a multinational group with corporate headquarters that have been situated in northern Italy since 1935.

Today we are a leader in the development, manufacturing and commercialization of advanced technical textiles & chemicals.

SAATI's passion and creativity are the foundation for an unsurpassed tradition of continuous innovation in the filtration markets. This endless pursuit is what drives SAATI's dedicated customercentric R&D to functionalize products beyond simple filtration.

SAATI's wide range of synthetic textiles and fabricated parts in Nylon, Polyester, Polypropylene, PEEK and PPS are the ideal engineered solution for demanding process filtration applications.

Through specialized processing and rigorous inspection, SAATI ensures consistent lot quality across tolerances, uniformity, strength, stability, and cleanliness for applications from 7 to 3,000 μm .

Perfecting the Art of Precision Woven Fabrics with Innovation Driven R&D and Strict Quality Controls


SAATImil is SAATI's dedicated line to the flour milling industry, which includes an extensive selection of fabric types that are manufactured in accordance with ISO 9001:2000 and in compliance with FDA Code of Federal Regulations, as well as with Regulations CE 1935/2004 and EU 10/2011.

To guarantee the reliability of our products we constantly run tests and have all the most updated and strict certifications that validate the consistency, performance, quality and characteristics of each item.

With about 1,000 employees worldwide, facilities and a strong, established track record in innovation and manufacturing excellence, our mission is to improve the life of every person every day, through working with customers and partners to create a safer, healthier and cleaner world.









Customer Focus

Customer Driven Innovation

Thanks to our direct presence in many countries, it is easy for customers to reach us, wherever they are located, and our response is always prompt. Our staff has a high level of technical expertise and dedication, and are always aiming to find the best solution for the customer's requirements.


SAATI sales representatives and engineers understand customers' applications, and work closely with staff in the production and R&D departments to offer a customized solution in a form that best meets their needs.

The quality of SAATI's food products is backed by the dedication and expertise of SAATI's customer service. Thanks to offices, warehouses, storage and fabrication facilities throughout the world, SAATI provides strong local support, expert responses to customer inquiries, strong engineering capability, technical support and fast delivery around the world.





SAATImil Fabrics



- mesh opening
- thread diameter

SAATImil Fabrics Key Features

- Monofilament woven fabrics
- Available in synthetic (PA-PES-MAR) fibers
- High open area
- Consistent geometrical tolerances
- Excellent strength and dimensional stability
- High resistance to mechanical stress, abrasion, chemical agents and corrosion
- Lot-to-lot consistency
- Longer screen life
- Intended to come into contact with food

Compliance of SAATImil Mesh Intended to Come into Contact with Food

Compliance of Composition:

Monofilament yarn polymer is in compliance with FDA Code of Federal Regulations (USA), Food and Drugs, Title 21, Part 177 Paragraph 177.1500 and 177.1420 (Indirect food additions: Polymers).



Compliance of Performance: Compliance with Regulations 1935/2004/CE & EU 10/2011


Specifically SAATI ensures full traceability throughout the production chain, from raw material to finished products vs. Customer. Mesh is tested in order to verify migration limits as per regulatories concerning plastic materials intended to come in contact with food.

The processes of SAATI are conducted in compliance with specific GMP.





SAATImil Weave Types



saatimil GG or Grit Gauze grades are woven with coarser opening sizes with a smaller fiber to provide a higher screening capacity.


SAATImil XXX grades have a large fiber size and are used for hard grades of wheat and durum or other abrasive grains.



A large fiber improves screen life, but decreases screen flow capacity.

A smaller fiber will provide greater screening capacity but will wear out faster.

The flour milling industry has traditionally used a unique numbering system to denote variations in fiber sizes.



SAATImil HT are high-capacity screens in medium and finer opening sizes. They have a higher tensile strength and better abrasive resistance than the SAATImil XX grades. They are ideal for the newer type sifting frames which have glued-on screens requiring high tensile stretching.

SAATImil XX fabrics are woven with two smaller diameter fibers adjacent to one another. This construction provides a rougher surface to the screen, which is beneficial when sieving soft wheat, bakery flour, and other products that are difficult to sift.

SAATIMII HS are high-strength fabrics produced with thicker and stronger yarns for longer durability. They are suitable for turbo-sifter covers and centrifugal sifters.








SAATImil PA GG

Grit Gauze grades are woven with coarser opening sizes with a smaller fiber to provide a higher screening capacity

Engineered especially for separation of coarser particles, SAATImil™ GG or Grit Gauze grades are woven with coarser opening sizes made by smaller fiber to provide a higher screen capacity. Thanks to this mesh design, SAATImil™ GG screens are suitable for plansifter and purifier machines.

- FDA Approved polymer
- Melamine Free
- Resistant to humidity changes
- Maintains tension







Product	Mesh Opening	Open Area	Mesh Count		Thread Diameter
	μm	%	cm	in	μm
PA 10 GG	1920	64	4.25	11	500
PA 12 GG	1800	61	4.5	11	500
PA 14 GG	1600	61	5	13	450
PA 15 GG	1400	62	5.5	14	400
PA 16 GG	1320	56	6	15	400
PA 17 GG	1250	56	6.5 x 5.75	17 x 15	400
PA 18 GG	1180	55	6.5	17	400
PA 19 GG	1120	59	7	18	325
PA 20 GG	1000	57	7.5	19	325
PA 22 GG	950	58	8	20	300
PA 23 GG	900	56	8.3	21	300
PA 24 GG	850	55	9	23	280
PA 26 GG	800	54	9.5	24	280
PA 27 GG	750	55	10.5	27	250
PA 28 GG	710	54	10.75	27	250
PA 30 GG	670	52	11	28	250
PA 31 GG	630	51	11.5	29	250
PA 32 GG	600	50	12	30	250
PA 34 GG	560	51	12.7	32	225
PA 36 GG	530	49	13.5	34	225
PA 38 GG	500	47	14	36	225
PA 40 GG	475	49	15	38	195
PA 42 GG	450	46	15.5	39	195
PA 44 GG	425	46	16	41	195
PA 45 GG	400	46	17	43	195
PA 47 GG	375	43	18	46	180
PA 48 GG	365	43	18	46	195
PA 50 GG	355	51	20	51	150
PA 52 GG	335	49	20.5	52	150
PA 54 GG	315	47	22	56	150
PA 58 GG	300	46	23	58	140
PA 60 GG	280	43	24	61	140
PA 62 GG	275	41	24	61	150
PA 64 GG	265	47	26	66	120
PA 66 GG	250	46	27	69	120
PA 68 GG	243	43	27.5	70	120
PA 70 GG	236	44	28	71	120
PA 72 GG	224	42	29	74	120
PA 74 GG	212	40	30	76	120








SAATImil PA XXX

SAATImil XXX Grades have a large fiber size and are used for hard grades of wheat and durum or other abrasive grains.

Characterized by large fiber size, SAATImil™ XXX range of woven screens is used for fine particle separation such as hard grades of wheat and durum or other abrasive grains. SAATImil™ XXX screens are used for plansifter and purifier machines.

- FDA approved polymer
- Monofilament woven meshes
- High open area
- Mesh opening from 300 μm to 80 μm
- Maintains tension
- Consistent geometrical tolerances
- Longer screen life
- High resistance to mechanical stress, abrasion, chemical agents and corrosion





Product	Mesh Opening	Mesh Opening Open Area		Count	Thread Diameter
	Micron	%	cm	in	μm
PA 3 XXX	300	46	23	58	140
PA 4 XXX	280	43	24	61	140
PA 5 XXX	250	46	27	69	120
PA 6 XXX	212	40	30	76	120
PA 7 XXX	200	39	31	79	120
PA 8 XXX	180	43	36	91	100
PA 8.5 XXX	160	37	38	97	100
PA 9 XXX	150	39	41	104	90
PA 9.5 XXX	140	36	43	109	90
PA 10 XXX	132	39	46	117	80
PA 10.5 XXX	125	38	49	124	80
PA 11 XXX	118	35	51	130	80
PA 12 XXX	112	37	55	140	70
PA 12.5 XXX	105	32	55	140	80
PA 13 XXX	100	32	57	145	70
PA 14 XXX	90	30	62	157	70
PA 14.5 XXX	90	35	66	168	61
PA 17 XXX	80	32	71	180	61








SAATImil PA HT

High-capacity screens in medium and finer opening sizes. They have a higher tensile strength and better abrasive resistance than SAATImil XX grades.

SAATImilTM HT high-capacity woven screens are characterized by medium and small opening size for fine particles separation. They fit to recent type sifting frames, requiring high tensile stretching, for plansifter and purifier machines.

- FDA approved polymer
- Monofilament woven meshes
- High open area
- Plain weave
- Maintains tension
- Consistent geometrical tolerances
- Longer screen life
- High resistance to mechanical stress, abrasion, chemical agents and corrosion





Product	Mesh Opening	ng Open Area Mesh Count		Thread Diameter	
	Micron	%	cm	in	μm
PA 3 HT	300	51	23.5	60	120
PA 4 HT	280	51	25	64	120
PA 5 HT	250	51	28.5	72	100
PA 6 HT	212	47	32	81	100
PA 7 HT	200	43	34	86	100
PA 8 HT	180	43	36	91	100
PA 8.5 HT	160	42	40	102	90
PA 9 HT	150	43	43	109	80
PA 9.5 HT	140	41	45	114	80
PA 10 HT	132	42	49	124	70
PA 10.5 HT	125	41	51	130	70
PA 11 HT	118	41	53	135	70
PA 12 HT	112	42	57.5	146	61
PA 13 HT	100	38	62	157	61








SAATImil PA XX

Fabrics that are woven with two smaller diameter fibers adjacent to one another, making them rougher in order to sift difficult products.

SAATImil XX screens are woven with two smaller diameter fibers adjacent to one another. This type of screen construction increases its surface roughness to the screen, bringing benefits in sieving soft wheat, bakery flour and other products that are more difficult to sift.

- FDA approved polymer
- Monofilament woven meshes
- Double warp structure
- Mesh opening from 212 μm to 85 μm
- High open area
- Maintains tension
- Consistent geometrical tolerances
- Longer screen life
- High resistance to mechanical stress, abrasion, chemical agents and corrosion
- Recommended for plansifters





Product	Mesh Opening	Open Area	Mesh Count		Thread Diameter
	μm	%	cm	in	μm
PA 6 XX	212	47	30/36	76/91	(90+2x61)/80
PA 7 XX	200	48	33/36	84/91	(80+2x61)/80
PA 8 XX	180	46	36/40	91/102	(80+2x61)/70
PA 8.5 XX	160	44	39/43	99/110	(70+2x61)/70
PA 9 XX	150	44	41/48	104/121	(70+2x61)/61
PA 9.5 XX	140	43	43/50	110/127	(61+2x60)/60
PA 10 XX	132	44	47/52	120/132	(61+2x50)/61
PA 10.5 XX	125	40	49/54	124/137	(61+2x50)/61
PA 11 XX	118	42	50/59	128/151	(61+2x50)/50
PA 12 XX	112	40	52/62	132/157	(61+2x50)/50
PA 12.5 XX	106	40	56/64	142/163	(61+2x44)/50
PA 13 XX	100	38	57/67	145/169	(61+2x50)/50
PA 14 XX	95	38	61/69	156/175	(50+2x44)/50
PA 14.5 XX	90	35	94/71	234/175	(50+2x44)/50
PA 15 XX	85	34	65/74	165/188	(50+2x43)/50








SAATImil PA HS

SAATIMII HS are high-strength fabrics produced with thicker and stronger yarns for longer durability. They are suitable for turbo-sifter covers and centrifugal sifters.

- FDA Approved polymer
- Plain weave
- Monofilament extra-strong woven meshes
- Thicker thread diameters
- Consistent geometrical tolerances
- High resistance to mechanical stress, abrasion, chemical agents and corrosion
- Longer screen life
- Resistant to humidity changes
- Maintains tension





Product	Mesh Opening	Open Area	Mesh Count		Thread Diameter
	Micron	%	cm	in	μm
PA 3 HS	300	34	19.5	49.5	200
PA 5 HS	250	34	23	58	170
PA 6 HS	210	34	29.5	75	140
PA 8 HS	165	32	34	86	120
PA 9 HS	150	39	41	104	90








SAATImil PES GG

Grit Gauze grades are woven with coarser opening sizes with a smaller fiber to provide a higher screening capacity

Engineered especially for separation of coarser particles, SAATImil™ GG or Grit Gauze grades are woven with coarser opening sizes made by smaller fiber to provide a higher screen capacity. The rough fabric surface makes the product remain longer on the sieves. This leads to better separation.

- FDA Approved polymer
- Melamine Free
- Resistant to humidity and temperature changes
- Maintains tension







Product	Mesh Opening	Open Area	Mesh	Count	Thread Diameter
	μm	%	cm	in	μm
PES 10 GG	2000	51	3.6	9.2	800
PES 12 GG	1800	61	4.25	11	500
PES 14 GG	1600	64	5	13	460
PES 15 GG	1400	57	5.4	13.7	450
PES 16 GG	1320	59	5.8	14.7	400
PES 18 GG	1180	58	6.5	17	385
PES 19 GG	1120	56	6.5	17	400
PES 20 GG	1000	57	7.5	19	320
PES 22 GG	950	58	8	20	300
PES 23 GG	900	56	8.3	21	300
PES 24 GG	850	55	9	23	280
PES 26 GG	800	55	9.5	24	280
PES 27 GG	750	53	10	25	260
PES 28 GG	710	52	10.5	27	260
PES 30 GG	670	52	10.8	27	260
PES 31 GG	630	53	11.5	29.2	240
PES 32 GG	600	51	12	30	240
PES 34 GG	560	47	12	30	260
PES 36 GG	530	50	13.4	34	220
PES 38 GG	500	48	14	36	220
PES 40 GG	475	50	15	38	200
PES 42 GG	450	48	15.4	39.1	200
PES 44 GG	425	46	16	41	200
PES 45 GG	400	52	18	46	160
PES 47 GG	375	50	19	48	160
PES 50 GG	355	47	19.4	49.3	160
PES 52 GG	335	46	20.2	51	160
PES 54 GG	315	46	21	53	160
PES 56 GG	300	44	23	58	145
PES 60 GG	280	43	24	61	145
PES 64 GG	265	53	27	69	100
PES 66 GG	250	44	27	69	120
PES 70 GG	236	41	29	74	120
PES 72 GG	224	35	27	69	145









SAATImil MAR


Specially Treated Mesh that Resists Moisture Absorption

SAATImil MAR™ is obtained from an advanced melamine free and FDA approved polymer then is woven and finished complex techniques. The MAR HT and MAR XX lines of fabric are the ideal choice for all milling applications where standard nylon cloths do not stand high humidity values and subsequently adsorb moisture, causing a critical loss of tension and decreased screening efficiency.

- FDA Approved polymer
- Melamine Free
- Resistant to humidity changes
- Maintains tension







Product	Mesh Opening	Open Area	Mesh O	pening	Thread Diameter
	Micron	%	cm	in	μm
3 HT	300	50	24	61	120
4 HT	280	44	23	58	145
5 HT	250	44	27	69	120
7 HT	200	45	36	91	90
8 HT	180	41	34	86	100
8.5 HT	160	42	38	97	90
9 HT	150	43	43	109	80
9.5 HT	140	40	45	114	80
10 HT	132	40	49	124	70
10.5 HT	125	41	55	140	64
11 HT	118	38	51	130	70
12 HT	112	29	46	117	90
13 HT	100	33	55	140	70
9 XX	150	40	40/48	101/122	(70+2x64)/64
10 XX	132	43	47/52	119/132	(60+2x48)/48
11 XX	118	41	50/61	127/155	(64+2x48)/48
12 XX	112	40	51/61	129/155	(64+2x48)/48








SAATImil STS

Woven Stainless Steel for Abrasive Sifting

SAATImil STS is a range of stainless steel woven meshes designed to sieve accurately abrasive materials including food, chemical products, stones and a variety of powders.

- Uniform pore size Consistent wire diameter
- Resistant to humidity
- Static loadingAccurate sizing
- Consistent geometric tolerancesLonger sieving operating life



Product	Mesh Opening		Open Area	Wt.		ire neter
SAATImil STS	μm	inch	%	kg/m²	μm	inch
STS 10 2240/74	2240	0.0882	74	0.65	360	0.0142
STS 11 2000/74	2000	0.0787	74	0.56	320	0.0126
STS 12 1800/72	1800	0.0709	72	0.61	320	0.0126
STS 14 1600/77	1600	0.0630	77	0.34	220	0.0087
STS 16 1400/75	1400	0.0551	75	0.38	220	0.0087
STS 17 1250/72	1250	0.0492	72	0.42	220	0.0087
STS 18 1180/71	1180	0.0466	71	0.44	220	0.0087
STS 19 1120/70	1120	0.0464	70	0.46	220	0.0087
STS 20 1060/69	1060	0.0417	69	0.48	220	0.0087
STS 21 1000/67	1000	0.0394	67	0.51	220	0.0087
STS 22 950/68	950	0.0374	68	0.44	200	0.0079
STS 23 900/67	900	0.0354	67	0.46	200	0.0079
STS 24 850/66	850	0.0334	66	0.48	200	0.0079
STS 26 800/64	800	0.0315	64	0.52	200	0.0079
STS 27 750/65	750	0.0295	65	0.44	180	0.0071
STS 28 710/64	710	0.0279	64	0.46	180	0.0071
STS 30 670/65	670	0.0264	65	0.40	160	0.0063
STS 32 630/64	630	0.0248	64	0.41	160	0.0063
STS 34 600/62	600	0.0236	62	0.42	160	0.0063
STS 35 560/60	560	0.0220	60	0.45	160	0.0063
STS 36 530/59	530	0.0209	59	0.47	160	0.0063
STS 38 500/57	500	0.0197	57	0.49	160	0.0063
STS 40 475/56	475	0.0187	56	0.52	160	0,0063
STS 42 450/58	450	0.0177	58	0.42	140	0.0055
STS 43 465/62	465	0.0183	62	0.34	125	0.0049
STS 44 425/57	425	0.0167	57	0.44	140	0.0055
STS 46 450/64	450	0.0177	64	0.29	112	0.0044
STS 46 400/54	400	0.0157	54	0.46	140	0.0055
STS 48 425/63	425	0.0167	63	0.30	112	0.0044
STS 50 400/61	400	0.0157	61	0.32	112	0.0044
STS 50 375/53	375	0.0148	53	0.48	140	0,0055


Product	Mesh Opening		Open Area	Wt.		ire neter
SAATImil STS	μm	inch	%	kg /m²	μm	inch
STS 52 375/59	375	0.0148	59	0.33	112	0.0044
STS 52 355/51	355	0.0140	51	0.51	140	0.0055
STS 54 375/62	375	0.0148	62	0.27	100	0.0039
STS 54 335/50	335	0.0132	50	0.53	140	0.0055
STS 56 355/61	355	0.0140	61	0.28	100	0.0039
STS 58 335/59	355	0,0132	59	0.29	100	0.0039
STS 58 315/54	315	0.0124	54	0.37	112	0.0044
STS 60 325/58	325	0.0128	58	0.30	100	0.0039
STS 62 315/58	315	0.0124	58	0.31	100	0.0039
STS 62 300/53	300	0.0118	53	0.39	112	0.0044
STS 64 300/56	300	0.0118	56	0.32	100	0.0039
STS 66 280/51	280	0.0110	51	0.41	112	0.0044
STS 68 280/54	280	0.0110	54	0.33	100	0.0039
STS 70 265/53	265	0.0104	53	0.35	100	0.0039
STS 72 250/51	250	0.0098	51	0.36	100	0.0039
STS 76 236/49	236	0.0093	49	0.38	100	0.0039
STS 78 224/48	224	0.0088	48	0.39	100	0.0039
STS 80 218/47	218	0.0086	47	0.40	100	0.0039
STS 84 212/49	212	0.0083	49	0.34	90	0.0035
STS 88 200/48	200	0.0079	48	0.36	90	0.0035
STS 88 190/43	190	0.0075	43	0.45	100	0.0039
STS 90 190/46	190	0.0075	46	0.37	90	0.0035
STS 90 180/41	180	0.0071	41	0.46	100	0.0039
STS 94 180/44	180	0.0071	44	0.38	90	0.0035
STS 94 170/40	170	0.0067	40	0.48	100	0.0039
STS 105 160/47	160	0.0063	47	0.25	75	0.0029
STS 120 140/47	140	0.0055	47	0.26	65	0.0026
STS 135 125/44	125	0.0049	44	0.28	65	0.0026
STS 145 118/46	118	0.0046	46	0.23	56	0.0022
STS 165 100/44	100	0.0039	44	0.21	50	0.0020
STS 180 95/46	95	0.0037	46	0.18	45	0.0018







Fabricated Components



Dust Filter Bags

Custom dust filter bags produced for most standard OEM baghouses. DFB's are available with materials PES, PP, and Nomex with surface finishing plain, singed, eggshell or PTFE. Seams can be sewn or heat welded. DFB's can be made top with raw edge, beaded cuff, or snap band.



Purifier Covers

SAATImil also manufactures purifier covers for all types of machines. The purifier covers can be manufactured either with PA GG or PES GG, with or without plastic rods and with rounded corners. SAATI Purifier Covers are intended to come in contact with food, and results of overall and specific migration tests are always available.



Intended to Come In Contact with Food



Centrifugal Sifting Screens

SAATImil manufactures sifting screens for all centrifugal sifter types, in a variety of designs. With capabilities to sew multifilament edges and seams, or welding urethane to the SAATImil mesh, SAATI has durable products that provide a consistent separation.

Our urethane seams ensure a solid product that does not show wear and tear. In addition, with urethane edging, it provides sanitary screens that can be washed and cleaned with little contamination.

Specific SAATI Centrifugal Sifting Screens are intended to come in contact with food, and results of overall and specific migration tests are always available.



Intended to Come In Contact with Food







Connector Sleeves

SAATImil is SAATI's dedicated line for the flour milling industry, which includes an extensive selection of fabric types that are manufactured in accordance with ISO 9001:2000 and in compliance with current food regulations.

SAATImil Connector Sleeves ensure a permanent and secure connection between plansifter, purifier, milling equipment, and inlet and outlet devices. The fabrication, developed for this specific application, is able to grant the correct behavior for each miller's needs. The SAATImil Connector Sleeves are made with food grade polyester multifiilament material that is compliant with FDA and EU 10/2011 regulation. This is proven by a migration test that has to be available and that SAATI can supply on request. Yarn used for assembly is food grade as well, in order to avoid any cross contamination for accidental flour contact during charge and discharge operation. Thanks to the material's elasticity SAATImil Connector Sleeves are resistant to the plansifter's continuous movement, granting excellent lifetime and performance that have been tested for years by the major milling equipment manufacturers. SAATImil Connector Sleeves can be fabricated to customer specification and according to the equipment standard sizes. SAATI can also fit all customer requirements for other configurations made with ends enclosing shock cord, elastic, draw string, or hems. Sleeves can also be produced with or without support rings.



Features

- Fully FDA Polymer Approved Conformity Declaration upon request
- Fully Compliant with EU 10/2011 Conformity Declaration upon request
- Excellent lifetime
- · High air permeability
- Tailor-made fabrication

Product	Dian	Diameter		Length	
Product	mm	inch	mm	inch	Ring n°
MPET 7338 Food Grade	300	11.8	310	12.2	2
MPET 7338 Food Grade	240	9.5	280	11	2
MPET 7338 Food Grade	210	8.3	310	12.2	2
MPET 7338 Food Grade	150	6	290	11.4	2
MPET 7338 Food Grade	120	4.7	290	11.4	2
MPET 7338 Food Grade	120	4.7	150	6	1
MPET 7338 Food Grade	120	4.7	260	10.2	2
MPET 7338 Food Grade	120	4.7	110	4.3	0

Other sizes, different from standard ones, are available upon request.



Photo courtesy of Lantmännen and FilTrade







SAATI Tendimesh

Rapidly Stretch Screens Off-Contact with Durable, Intuitive Stretch Clamps

SAATI Tendimesh is the newest screen stretching system, specially developed for the milling industry. Thanks to the combination of our competency and experience with technical meshes in milling applications, we offer a new product that confers significant advantages in milling screen production.

SAATI Tendimesh is a modular system with the option to use two different jaw sizes, and with a choice between single and double pressure circuits through the use of two different control panels.

This flexibility guarantees compatibility with different frame types (metal or wood) and sizes (i.e. 710x655 cm, 570x620cm, 570x500 cm). The assembly option

with two circuit panels facilitates independent very fine tuning on the X & Y axes, in order to achieve equal tension in the warp and weft directions.

SAATI Tendimesh is a compact device with a small footprint, built with high quality materials and a reliable mechanism.

SAATI Tendimesh clamps lock mechanically instead of pneumatically, so in the event of a loss of pressure, the mesh will remain secured in the jaws.

The system works with a dedicated table and line of accessories that enable you to tension every type of fabric on every type of frame.

SAATI Tendimesh Specifications					
Jaw Width	24.8 or 28.7" 63 or 73 cm				
Maximum Tension	15.9 lb/sq. in. at 100 psi 28 N/cm at 7 bar				
Clamp Weight	55.1 lbs 25 kg				
Piston Stroke	1.96" 50 mm				
Clamp Total Length	13" 331 mm				
Clamp Length to Contact Point with Frame	10.91" 277 mm				
Colors	RAL 9001 - standard				
Control Panel	Pneumatic switches for handling tension / pressure gauge / emergency lock				
Compressed Air	95-100 PSI (humidity free air line required)				
Recommended Table Size	59 x 59" 1500 x 1500 mm				





















Tendimesh Accessories

Tensioning Support








≤ 112 micron

≤ 140 micron

≤ 200 micron

Frame Spacer



MDF Support





- 620 x 30 h40 mm
- 620 x 30 h47 mm
- 720 x 30 x h40 mm
- 720 x 30 x h47 mm

Suitable for both wood and metal frame.



Dimensions

- 620 x 30 x 47-53 mm
- 720 x 30 h47-53 mm



SAATImil Tension Meter

Quickly and easily determine the tension for screens both in the process of stretching and before, during and after use

The Newman ST-Meter is a uniquely constructed, heavy-duty mechanical tension meter that assures durability and long-term accuracy in monitoring screen tension. It is the only meter in the world with all stainless steel hardened gears, shock-proof industrial grade internal gear movementand all jeweled sapphire bearings.

A screen tension meter of exceptional quality will produce accurate readings consistently fora very long time. All other mechanical meters have softer brass gears and bushings that greatly reduce their life and accuracy. The crystal is shatter proof and curved to reduce glare. The heavy-duty protective aluminum housing is the most durable meter made anywhere.

The modular construction assures easy and inexpensive repairs, if any are necessary.

Key Features

- Shock-proof unitized internal gear movement
- Eight sapphire jeweled bearings
- Six compound hardened stainless steel gears
- Also available in kilograms/meter
- Direct reading in N/cm, ±1% accuracy
- Shatterproof crystal
- · Heavy-duty protective aluminum housing
- A calibration plate is provided with each meter, and is packaged in a protective carrying case



Technical Data					
Test Conditions		50/60% Humidity 18-20°C			
Measuring Range		5-60 N/cm			
Sifter Mesh Opening(µm)	Original Tension N/cm		Tension after 3 hours N/cm		
SAATImil PA >375	16-14		13-8		
SAATImil PA 355-280	14-12		11-7		
SAATImil PA 270-150	12-10		9-6		
SAATImil PA 140-80	10-8		7-5		
Weight of the Newman ST-Meter		2.2 lbs			

SAATImil Adhesives





SAATI Ultrafix CA adhesives are designed for bonding wire cloth and synthetic screens to wood, metal or plastic frames. Ultrafix CA adhesive is available in 50 and 450 gram containers.

Poly Squeegee (Scrapers)

Poly Squeegee (scrapers) are available in 5 x 7.5 cm



Ultrafix CA Activator

Ultrafix CA Activator cures cyanoacrylate adhesive instantly and is available in two types of dispensers: aerosol and pump. It is available in 200 ml containers.

Ultrafix Remover

Ultrafix Remover is a convenient gel which removes Ultrafix adhesives. This gel is effective on urethane-based and cyanoacrylate adhesives.

Ultrafix Remover is available in 1 and 5 kg containers.

Ultrafix Product	Viscosity
Ultrafix CA 150	Very High
Ultrafix CA 100	High
Ultrafix CA 50	Medium
Ultrafix CA 5	Low







Filip Sieve Cleaners





SAATI offers an assortment of Filip sieve cleaners that will help you to maximize your milling yield. Filip has been developing and producing sieve cleaners for over 100 years. The carefully calibrated design, selected materials and weight of Filip products imbue them with the efficiency, durability and safety that continually position them as the highest quality sieve cleaners available.



Style 100: Sieve Cleaning **Brush with Solid Stainless** Steel Slider Knob, Black Nylon Bristles for Wire Mesh



Style 101: Sieve Cleaning Brush with Solid Stainless Steel Slider Knob Natural Hair for Synthetic Mesh



Style 102: Sieve Cleaning **Brush with Solid Stainless** Steel Slider Knob White Nylon Bristles for Synthetic Mesh



Style 110: Sieve Cleaning Brush with Solid Stainless Steel Slider Knob Black Nylon Bristles for Wire Mesh - Large Model



Style 111: Sieve Cleaning Brush with Solid Stainless Steel Slider Knob Natural Hair for Synthetic Mesh - Large Model



Style 112: Sieve Cleaning Brush with Solid Stainless Steel Slider Knob White Nylon Bristles for Synthetic Mesh - Large Model



Style 120: Sieve Cleaning Brush with Plastic Slider Knob Black Nylon Bristles for Wire Mesh - Large Model



Style 121: Sieve Cleaning Brush with Plastic Slider Knob Natural Hair for Synthetic Mesh - Large Model



Style 122: Sieve Cleaning Brush with Plastic Slider Knob White Nylon Bristles for Synthetic Mesh - Large Model



Style 200: Sieve Cleaner with Studs with Solid Stainless Steel Slider Knob



Style 201: Sieve Cleaner with Studs with Plastic Slider Knob



Style 210: Sieve Cleaner with Studs with Solid Stainless Steel Slider Knob - Large Model





Filip Sieve Cleaners



Style 211: Sieve Cleaner with Studs with Plastic Slider Knob - Large Model



Style 1103: Blue Sieve Cleaning Brush with Solid Stainless Steel Slider Knob Blue Nylon Bristles for Synthetic Mesh



Style 1200: Blue Sieve Cleaner with Studs with Solid Stainless Steel Slider Knob



Style 1201: Blue Sieve Cleaner with Studs with Plastic Slider Knob



Style 150: Double Cleaner with Black Nylon Bristles for Wire Mesh



Style 151: Double Cleaner with Natural Hair for Synthetic Mesh





Style 152: Double Cleaner with White Nylon Bristles for Synthetic Mesh



Style 250: Double Cleaner with Studs for Wire & Synthetic Mesh



Style 1153: Blue Double Cleaner with Blue Nylon Bristles for Wire Mesh



Style 1250: Blue Double Cleaner with Studs for Wire & Synthetic Mesh



Style 301: Pan Cleaner with Recess



Style 1301: Blue Pan Cleaner with Recess





Sieve Cleaners



Cotton Cleaner Green Stripe

First quality cotton cleaner made from densely woven material to create a hard surface.

Strong quality threads increase the endurance of the material and life of the cleaner.



Cotton Cleaner Blue Stripe

Second quality cotton cleaner having a softer surface as for 15% less threads in weft.



Triangular Type Sieve Cleaner with Brushes & Solid Metal Slider Knob

Designed for cleaning all types of synthetic mesh material with gentle brushes. Cleans back-wire with action of metal slider knob. Available with nylon bristles or natural hair.



Triangular Type Sieve Cleaner with or without Plastic Studs and Metal Slider Knob

Designed for all meshes 200 µm & up. Cleans back-wire with action of metal slider knob.



Light Plastic Sieve Cleaner with Metal Slider Knob in Desmopan

Designed for cleaning all types of meshes. Cleans back-wire with action of metal slider knob.



Triangular Pan Cleaner in Desmopan

High elasticity polyurethane provides effective cleaning without damaging sieve frames.



Diamond Plastic Pan Cleaner Round or Diamond Center

High elasticity polyurethane provides effective cleaning without damaging sieve frames.







Sieve Cleaners



Rectangular Sieve Cleaner

Rectangular in shape, used to keep sifting material clean with the movement and action of the sifter. This cleaner used in sieve trays with back wire



Sieve Balls

Sieve balls used to keep mesh material clean. Available in a variety of sizes: 16, 25, 30 and 35 mm Ø. Materials: polyurethane, rubber and silicone



Bühler Nova Plastic Sieve Cleaners with Knobs or Brushes

Three prong cleaner with a center bottom support and leg extending from one of the prongs. This leg gives a "teeter-totter" effect to keep the sieve cloth cleaner and free of product build-up. Made from flexible polyurethane materials with knobs as used on heavy synthetic and wire cloth materials. Designed for use in Bühler Nova Sieves



Brushes for Purifiers

85 mm. Space between guides, tuft mounting frame in plastic, oscillating central body in nylon. Available in Synthetic, Animal & Horsehair. Dimensions available are 390-440-350-455-460.

Accessories



Pneumatic Stapler

Pneumatic stapler for staple on sieves for use with industrial strength staples.



Stretching Pliers

Stretching pliers used the pull stretch sifter clothing in order to staple edge to perimeter of sieve tray.



Rubber Mallet

Rubber mallet made with heavy duty plastic handle. Available in black or white color.







Accessories



Spatula

Spatula (flour slick) with a broad, flat, blunt blade used for spreading flour to examine the particle size.



Scraping Knife

Scraping knife used to remove excess glue from surface of sieve.



Plush

Thick plush for inner isolation of plansifters. Available in widths of 140 cm.



Protective Tapes

1.8 mm thick polyester felt tape. Available in 10, 15 and 20 mm width.

Accessories



Microscope

Microscope for measurement viewing of mesh materials up to 40x.



10x Mesh Counter

Small foldable mesh counter in both inches and mm measurements.



Brush for Break Rolls

In whole goose feather. Available in lengths of 1000 and 1250 mm.







Interactive Product Index

Click a page number to view the product/topic

0-9	G	S
10x Loop 41	Grit Gauze 8, 10	SAATImil Fabrics 7
10x Magnifier 41		SAATImil GG Grit Gauze 8
10x Mesh Counter 41	I	SAATIMII HS 9
	ISO 9001:2000 3	SAATImil HT 9
Α	М	SAATImil MAR 22
Adhesives 31	Market Grade Stainless	SAATImil PA GG 10
В	Steel Mesh 25	SAATImil PA HS 18
Bolting Cloth Grade	MAR Mesh 22	SAATImil PA HT 14
Stainless Steel Mesh 25	Microscope 41	SAATImil PA XX 16
Break Roll Brush 41	Mill Grade Stainless	SAATImil PA XXX 12
Brushes for Purifiers 38	Steel Mesh 25	SAATImil PES GG 20
Brush for Break Rolls 41	Moisture Absorption Resistant Mesh 22	SAATImil STS 24
Bühler Nova Plastic	Monofilament 7	SAATImil Tension Meter 30
Sieve Cleaners 38		SAATImil Weave Types 8
С	P	SAATImil XX 9
Centrifugal Sifters 18, 26	PA GG Mesh 10	SAATImil XXX 8
Centrifugal Sifting Screens 26	PA HS Mesh 18	SAATI Tendimesh 28
Company Information 3	PA HT Mesh 14	Scrapers 31
Compliance of Composition 7	Pan Cleaner 35, 37	Scraping Knife 40
Compliance of Performance 7	PA XX Mesh 16	Screen Cleaners 32, 36
Connector Sleeves 27	PA XXX Mesh 12	Sieve Cleaner 34, 36, 38
Cotton Cleaner 36	PES GG Mesh 20	Sieve Cleaning Brush 32
Customer Service 5	Plastic Sieve Cleaner 37	Spatula 40
	Plush 40	Stainless Steel Woven Mesh 24
D	Pneumatic Stapler 39	Stretching Clamps 28
Dust Filter Bags 27	Poly Squeegee (Scrapers) 31	Stretching Pliers 39
F	Purifier Brushes 38	Т
-	Purifier Covers 26	_
Fabricated Components 26	R	Tension Meter 30
FDA Code 7		Turbo-Sifter Covers 18
FDA Code 7	Regulation EU 10/2011 3 Regulations CE 1935/2004 3	U
Filip Screen Cleaners 32 Frame Adhesives 31	Rubber Mallet 39	Ultrafix CA Activator 31
Traine Adirestives VI	Number Mullet 07	Ultrafix CA Series Adhesives 31

Ultrafix Remover 31

Notes

Take notes before you contact **SAATI Customer Service**

_	
	l
1	
1	
I .	
	l





S/4\TI

SAATI S.p.A

Via Milano, 14

22070 Appiano Gentile (Co), Italy

Fax: +39 031 933392 E-mail: info.it@saati.com

SAATI Americas Corp.

201 Fairview St. Extension Fountain Inn, SC 29644 Toll-Free: +1 800 431 2200 Fax: +1 864 862 0089 E-mail: info.us@saati.com

SAATI Technical Fabrics (Tianjin) Co., Ltd.

Cross Of Saida 2nd Branch Road and Saida Century Avenue, Xiqing Economic Development Area,

Tianjin, China 300385 Tel: +86 22 23960843 Fax: +86 22 23962116 E-mail: info.cn@saati.com

SAATI Korea Ltd.

22, Dangjeong-ro, Gunpo-si Gyeonggi-do, 435-833, Korea

Phone: +82 31 429 9337 Fax: +82 31 429 9338

SAATI France

74 Route de Bapaume 80360 Sailly Saillisel, France

Phone: +33 3 22 85 77 00 Fax: +33 3 22 85 77 00 E-mail: info.fr@saati.com

SAATI Deutschland GmbH

Ostring 22 46348 Raesfeld, Germany

Phone: +49 2865 95800 Fax: +49 2865 958010 E-mail: info.de@saati.com

SAATI Serigrafía Ibérica, S.a.

Pol. Ind. El Mijares, C/ Industria, nº 13 12550

Almazora, Castellón, Spain Phone: +34 964550688 Fax: +34 964551049 E-mail: info.es@saati.com

SAATI Russia

23 Shvetsova str. 198095 Saint-Petersburg, Russia Phone: +79 062788343

10

Connect with SAATI











